

**SAFE AND SIMPLE TO USE.**

onica todescato **ARE UNIQUE.**

**GENERATORS OF HYDROGEN AND OXYGEN / MIXED GAS**

The operation principle of these generators is based on the electrolytic dissociation of water. Maintenance is extremely simple. Specially suitable for: Brazing in goldsmithing,

jewelry, eyewear, dentistry, glass processing, methacrylate polishing, precision electromechanical process, electronic.



**Mod. L/700**

**Mod. L/350**

**TECHNICAL SPECIFICATIONS**

Model	Mod. L/700	Mod. L/350
Gas production Lt/hour	700	350
Consumption of demineralized water Lt/hour	0,35	0,175
Consumption of alcohol cc/hour	115	57
Capacity of alcohol container Lt	3	0,68
Max. power absorbed kW-(220/230V)	3	1,5
Electrolyte quantity Lt	9	7
Overall dimensions LxDxH cm	60x75x35 cm	55x65x30
Weight Kg	130	95



**Mod. L/160**

**Mod. L/80**

**Mod. L/45**

**TECHNICAL SPECIFICATIONS**

Model	Mod. L/160	Mod. L/80	Mod. L/45
Gas production Lt/hour	160	80	45
Consumption of demineralized water cc/h	82	41	22
Consumption of alcohol cc/hour	30	15	9
Capacity of alcohol container cc	282	225	153
Max. power Watt - (220/230V)	950	590	280
Electrolyte quantity Lt	3	1	0,5
Overall dimensions LxDxH cm	46,5x41,5x33,5	38,5x36x28,5	28,5x29x23
Weight Kg	45	25	14